

Product data sheet

Specifications



Wall rack VDM 10U 2 bodies D380

NSYVD2M10U4

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	2-body
Rack Type	Fixed
Enclosure Nominal Height	500 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	380 mm
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 rear part: inside the enclosure 2 cable gland plate: top and bottom of rear 1 19" fixed rack: 65 mm back from the front panel 1 body 1 door with lock

Complementary

Door Type	Glazed
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Type Of Gland Plate	Standard
Number Of Units 19"	10
Accessibility For Operation	Front body and front rear
Removable Parts	Door by hinges Body by fixing element Rack
Material	Enclosure: steel 19" fixed rack: galvanised steel
Surface Finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
Net Weight	26 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	600 mm
Height	500 mm
Depth	380 mm

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	62.0 cm
Package 1 Width	54.0 cm
Package 1 Length	43.0 cm
Package 1 Weight	26.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile