

# Product data sheet

Specifications



## Floor-Standing Cabling Rack 42U W800D600 Fixed 19" Glazed Door R7035

NSYVDA42U86B

 To be discontinued on: Jun 30, 2024

 To be discontinued

### Main

Range	Actassi
Product Name	Actassi VDA
Product Or Component Type	19" enclosure
Device Application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure Type	Network Cabinet
Support Equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front Face	Glazed door
Door Type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180°
Accessibility For Operation	Top Side Front Rear
Removable Parts	Front door removable toolless Top blanking plate Bottom blanking plate Side panels removable toolless Rear panel removable toolless
Colour	Door: light grey (RAL 7035) Panels: light grey (RAL 7035) Top and bottom: light grey (RAL 7035) Structure: dark grey (RAL 7011)

### Complementary

Device Composition	1 x glazed door front 2 x panels side 2 x 19" uprights front 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 1 x panel rear 4 x levelling feets
Load Rating	400 kg static 250 kg dynamic
Back Face	Panel
Side Face	Panel
Number Of Cut-Out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Installation Mode	Floor-standing
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel
Surface Finish	Epoxy-polyester powder
Width	800 mm
Height	2000 mm
Depth	600 mm
Net Weight	96 kg
Number Of Rack Unit	42U
Targeted Region	Europe

## Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	IEC 60297-3-100 EIA-310D

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	85.0 cm
Package 1 Width	65.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	96.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations