

Product data sheet

Specifications



Floor-Standing Cabling Rack 24U W600D1000 Fixed 19" Glazed Door No Panel R9011

NSYVDAC24U610N

 **Discontinued on:** Sep 30, 2019

 **Discontinued**

Main

Range	Actassi
Product Name	Actassi VDA
Product Or Component Type	19" enclosure
Device Application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure Type	Network Cabinet
Support Equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front Face	Glazed door
Door Type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 ° Rear partial plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility For Operation	Rear Top Front Side
Removable Parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear partial door removable toolless Rear partial panel removable toolless
Colour	Door: black (RAL 9011) Panels: black (RAL 9011) Top and bottom: black (RAL 9011) Structure: black (RAL 9011)

Complementary

Device Composition	1 x glazed door front 2 x 19" uprights front 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feet 1 x partial panel (6U) rear 1 x partial plain door rear
Load Rating	400 kg static 250 kg dynamic
Back Face	Partial plain door
Side Face	Panel

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Cut-Out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts
Installation Mode	Floor-standing
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel
Surface Finish	Epoxy-polyester powder
Width	600 mm
Height	1200 mm
Depth	1000 mm
Net Weight	83 kg
Number Of Rack Unit	24U
Targeted Region	Europe

Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	IEC 60297-3-100 EIA-310D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	133 cm
Package 1 Width	70 cm
Package 1 Length	105 cm
Package 1 Weight	83 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile