


# Product data sheet

Specifications



## Floor-Standing Cabling Rack 42U W800D800 Fixed 19" Glazed Door No Panel R7035

NSYVDAC42U88

 **Discontinued on:** Dec 3, 2020

 **Discontinued**

### Main

Range	Actassi
Product Name	Actassi VDA
Product Or Component Type	19" enclosure
Device Application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure Type	Network Cabinet
Support Equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front Face	Glazed door
Door Type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 ° Rear partial plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility For Operation	Side Top Front Rear
Removable Parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear partial door removable toolless Rear partial panel removable toolless
Colour	Door: light grey (RAL 7035) Panels: light grey (RAL 7035) Top and bottom: light grey (RAL 7035) Structure: dark grey (RAL 7011)

### Complementary

Device Composition	1 x glazed door front 2 x 19" uprights front 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feet 1 x partial panel (6U) rear 1 x partial plain door rear
Load Rating	400 kg static 250 kg dynamic
Back Face	Partial plain door
Side Face	Panel

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Cut-Out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts
Installation Mode	Floor-standing
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel
Surface Finish	Epoxy-polyester powder
Width	800 mm
Height	2000 mm
Depth	800 mm
Net Weight	86 kg
Number Of Rack Unit	42U
Targeted Region	Europe

## Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213 cm
Package 1 Width	85 cm
Package 1 Length	85 cm
Package 1 Weight	86 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>