



Main

Range	Spacial
Product name	Spacial VDM
Application	Electronic application
Product or component type	Compact enclosure
Body type	1-body
Rack type	Fixed
Enclosure nominal height	500 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	400 mm
Installation accessory type	Wall-mounting
Product destination	Electronics and networks
Device composition	1 1 1 1 bottom

Complementary

Door type	Glazed
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Number of units 19"	10
Accessibility for operation	Front
Removable parts	Door by hinges Rack by fixing element
Material	Steel for enclosure Galvanised steel for 19" fixed rack
Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure :

Standards	IEC 62208
Product weight	21.4 kg

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------