

Product data sheet

Specifications



19" fixed chassis 8U Spacial

NSYVDM8UF

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application Multi-purpose
For Enclosure Nominal Dimensions	- H: 400 mm W: 600 mm D: 200 mm - H: 400 mm W: 600 mm D: 250 mm
Rack Type	Fixed
Mounting Location	Front of enclosure Step slide
Range Compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial VDM Spacial Spacial CRN
Device Composition	fixing elements 2 19" uprights
Number Of Units 19"	8

Complementary

Material	Galvanised steel
Enclosure/Cubicle Description	Wall-mounted enclosure
Fixing Mode	By fixing element
Adjustment	Adjustable in depth, pitch 12.5 mm, on the step slide
Colour	Grey (RAL 7035)
Permanent Permissible Load	3 kg per unit
Height	400 mm nominal:
Width	600 mm nominal:
Depth	420 mm
Thickness	2 mm
Net Weight	2.3 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10.5 cm
Package 1 Length	42.0 cm
Package 1 Weight	2.3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations