

# Product data sheet

Specifications



## Floor-Standing Server Rack 42U W800D1000 Fixed 19" Perf. Door No Panel R9011

NSYVDSC42U810N

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	Actassi
Product Name	Actassi VDS
Product Or Component Type	19" enclosure
Device Application	Server
Applications	To mount 19" equipment To mount server components To protect network connectivity equipment
Enclosure Type	Server cabinet
Support Equipment	4 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front Face	Microperforated door
Door Type	Front microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 ° Rear microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 °
Accessibility For Operation	Top Rear Front Side
Removable Parts	Front door removable toolless Bottom blanking plate Rear door removable toolless Top blanking plate equipped with brush gasket
Colour	Door: black (RAL 9011) Top and bottom: black (RAL 9011) Structure: black (RAL 9011)

### Complementary

Device Composition	1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feets 4 x 19" uprights 1 x microperforated door (airflow 80%) front 1 x microperforated door (airflow 80%) rear
Load Rating	750 kg static
Back Face	Microperforated door
Number Of Cut-Out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts
Installation Mode	Floor-standing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright
Surface Finish	Epoxy-polyester powder
Width	800 mm
Height	2000 mm
Depth	1000 mm
Net Weight	120 kg
Number Of Rack Unit	42U
Targeted Region	Europe

## Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	80.0 cm
Package 1 Width	100.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	120.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations