

Product data sheet

Specifications



Water drain plug, for drainage of condensation water. Drilling diam: 8.5 mm.IP53

NSYVEA9

Main

Range	Thalassa
Range Compatibility	Thalassa Thalassa PLM
Product Or Component Type	Plug
Accessory / Separate Part Category	Thermal management accessory
Environmental Characteristic	Water resistant
Mounting Location	Bottom of enclosure
Fixing Mode	Clipped
Device Composition	1 plug
Quantity Per Set	Set of 10

Complementary

Diameter	8.2 mm for PLM 8.5 mm
Ip Degree Of Protection	IP53 (category 2)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.76 cm
Package 1 Width	1.78 cm
Package 1 Length	1.78 cm
Package 1 Weight	1 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	400
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	577 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

 Reach Free Of Svhc

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations