

Product data sheet

Specifications



Polyester glassreinfr. plinth for encl.
PLAZ(T)73 front opening IP44-IK10
RAL7035

NSYZZ273G

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Plinth
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 2 front panel 2 side part
Range Compatibility	Thalassa Thalassa PLA

Complementary

Fixing Mode	By screws - on side parts location
Colour	Plinth: grey (RAL 7035)
Height	200 mm
Width	785 mm
Depth	310 mm

Environment

Ip Degree Of Protection	IP44
Ik Degree Of Protection	IK10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	46.0 cm
Package 1 Length	79.0 cm
Package 1 Weight	7.25 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations