



Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica Studio
Device presentation	Complete product
Socket number	2
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth

Complementary

Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Fixing mode	Screws
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Glossy
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 DIN VDE 0620-1 UNE 20315-1-1 UNE 20315-1-2
Product certifications	EAC Aenor
Embedding depth	24 mm
Depth	47 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	85 mm
Height	125 mm
Product weight	0.099 kg
Surface treatment	Untreated

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Liquid soap Window-cleaning fluid Petrol Ammonia Acetone Bleach UV resistant Oil Alcohol
Environmental health and issues	Halogen free