

Product data sheet

Specifications



Exiway - MLT - main monitoring

OVA18508

Main

Range	Exiway
Product Name	Exiway Power Control
Device Short Name	MLT
Product Or Component Type	Main monitoring
Device Application	Monitoring

Complementary

Range Compatibility	Exiway Exiway Power Control Exiway Power Control Pico central battery system Exiway Exiway Power Control Exiway Power Control Nano central battery system Exiway Exiway Power Control Exiway Power Control Mega central battery system Exiway Exiway Power Control Exiway Power Control Multi central battery system
[Ue] Rated Operational Voltage	230 V
Number Of Inputs	4 changeover contact
Input Voltage	230 V AC 30 V DC, 2 A
Depth	90 mm
Width	54 mm
Height	54 mm
Net Weight	0.24 kg

Environment

Ambient Air Temperature For Operation	-10...40 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	5.4 cm
Package 1 Length	9.0 cm
Package 1 Weight	290.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Compliant
	EU RoHS Declaration

China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)