

# Product data sheet

Specifications



## Exiway - MLT-MC - line monitor

OVA18509

### Main

Range	Exiway
Product Name	Exiway Power Control
Device Short Name	MLT-MC
Product Or Component Type	Line monitor
Device Application	Monitoring

### Complementary

Range Compatibility	Exiway Exiway Power Control Exiway Power Control Pico central battery system Exiway Exiway Power Control Exiway Power Control Nano central battery system Exiway Exiway Power Control Exiway Power Control Mega central battery system Exiway Exiway Power Control Exiway Power Control Multi central battery system
[Ue] Rated Operational Voltage	230 V
Number Of Inputs	4 line monitor
Input Voltage	230 V AC
Communication Port Support	RS485
Depth	90 mm
Width	54 mm
Height	54 mm
Net Weight	0.07 kg

### Environment

Ambient Air Temperature For Operation	-10...40 °C
---------------------------------------	-------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	5.4 cm
Package 1 Length	9.0 cm
Package 1 Weight	300.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---