



## Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency light fitting
Device application	Lighting
Function	Addressable
Supply	Non-maintained
Number of batteries	1 x 7.2 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	Fluorescent tube 2G11 24 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Dardo Plus control unit

## Complementary

Range compatibility	control unit
[Ue] rated operational voltage	220...230 V AC/DC 50 Hz
Power consumption in VA	7.5 VA
Power consumption in W	1.4 W
Current consumption	32 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Luminous flux	Emergency condition: 260 lm Maintained mode: 550 lm
Type of glass	Green glass
Material	Housing: plastic Cover: plastic
Device mounting	Surface ceiling

Hanging ceiling  
Flush false ceiling  
Flush wall  
Surface wall  
Electrified track

Height	160 mm
Width	375 mm
Depth	68 mm

## Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	IMQ
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------