

Product data sheet

Specifications



Astro Guida - emergency exit sign - addressable - maintained - 3 h

OVA34758E

⚠ Discontinued on: Dec 31, 2018

⚠ Discontinued

Main

Range	Exiway
Product Or Component Type	Emergency exit sign
Function	Addressable
Supply	Maintained
Wiring Device Additional Information	Brackets for flag installation included 5 pictogram stickers included Can be inhibited with rest mode via Dardo Plus control unit

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Power Consumption In Va	12 VA
Visibility Distance	24 m
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Autonomy	3 h
Charging Time	24 h
Bulb Type	Cold cathode light 40000 h
Electrical Insulation Class	Class II
Device Mounting	Surface ceiling Flag type bracket wall Hanging ceiling Surface wall Electrified track
Height	213 mm
Width	261 mm
Depth	35 mm
Net Weight	0.865 kg

Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK06 IK07 wall
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 50-11 IEC 60695-2-10 EN/IEC 60598-2-22 IEC 695-2-1 EN 1838
-----------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	27.8 cm
Package 1 Length	28.2 cm
Package 1 Weight	0.865 kg

Contractual warranty

Warranty	18 months
----------	-----------