



Main

Range	Exiway
Product name	Exiway Easyled
Product or component type	Emergency light fitting
Function	Self-test
Supply	Maintained
Number of batteries	1 x 3.6 V 1.6 Ah Ni-Cd (Nickel-Cadmium) battery
Light source	Integral LED : 4 x 0.5 W

Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	230 V at 50/60 Hz
Power consumption in VA	4 VA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Luminous flux	Emergency condition : 170 lm Maintained mode : 85 lm
Type of glass	Serigraphed transparent glass
Device mounting	Surface ceiling Surface wall Flush false ceiling Flush wall
Height	292 mm
Width	116 mm
Depth	37 mm
Product weight	0.53 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	ENEC
Standards	EN 62471 EN 60598-1 EN/IEC 60598-2-22 EMC directive

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1502 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information