

Product data sheet

Specifications



Exiway Class- emergency light block- self-diagnosis- non-maintained- 1 h- 260 lm

OVA38565

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

Main

Range	Exiway
Product Name	Exiway Class
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Self-test
Operational Mode	Non-maintained
Number Of Batteries	1 x 4.8 V 1.6 Ah Ni-Cd (Nickel-Cadmium)
Light Source	LED 11 W
Light Source Colour	White
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	5.6 VA
Power Consumption In W	1.3 W
Current Consumption	24 mA
Electrical Insulation Class	Class II
Autonomy	1 h
Charging Time	12 h
Type Of Glass	Mineral glass
Device Mounting	Flush wall Surface wall
Material	Housing: plastic Cover: glass
Height	223 mm
Depth	51 mm
Width	303 mm
Net Weight	1.49 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ CE
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10 EN/IEC 62471

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	24.4 cm
Package 1 Length	33 cm
Package 1 Weight	2.44 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information