



has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency light fitting
Function	Standard
Supply	Non-maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Light source	Fluorescent tube G5 6 W
Wiring device additional information	Can be inhibited via a switch

Complementary

[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	4.2 VA
Power consumption in W	2.7 W
Electrical insulation class	Class II
Autonomy	3 h
Charging time	24 h
Luminous flux	50 lm
Type of glass	Green glass
Device mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	146 mm
Width	300 mm
Depth	62 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

IP degree of protection	IP42
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	IMQ
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Contractual warranty

Warranty	18 months
----------	-----------