

Product data sheet

Specifications



Exiway One - emergency light block - standard - non-maintained - 3 h - 200 lm

OVA38648

⚠ Discontinued on: Dec 31, 2016

⚠ Discontinued

Main

Range	Exiway
Product Name	Exiway One
Product Or Component Type	Emergency luminaire
Function	Standard
Operational Mode	Non-maintained
Number Of Batteries	1 x 6 V 4 Ah Ni-Cd (Nickel-Cadmium)
Light Source	Fluorescent tube 2G11 18 W
Wiring Device Additional Information	Can be inhibited via a switch

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Power Consumption In Va	7 VA
Power Consumption In W	3.1 W
Electrical Insulation Class	Class II
Autonomy	3 h
Charging Time	24 h
Type Of Glass	Green glass
Device Mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	160 mm
Depth	68 mm
Width	375 mm

Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ
Ambient Air Temperature For Operation	0...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60598-2-22 IEC 60695-2-10
-----------	-------------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	8 cm
Package 1 Length	38.1 cm
Package 1 Weight	1.67 kg

Contractual warranty

Warranty	18 months
----------	-----------