



Main

Range of product	Top 4
Product or component type	Portable emergency lamp
Device application	Lighting
Colour	Red
Wiring device additional information	Colour filters included

Complementary

[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	10 VA
Device composition	Charging unit
Battery capacity	4 Ah 6 V lead-acid battery
Charging time	24 h
Bulb type	Xenon 5.4 W main lamp Incandescent 1.5 W auxiliary lamp
Autonomy	15 h auxiliary lamp 3 h main lamp
Luminous flux	320 lm 2 m main lamp 5 lm 1 m auxiliary lamp
Operating mode options	Main lamp : blinking Auxiliary lamp : blinking
Enclosure material	Plastic
Electrical insulation class	Class II
Length	262 mm
Height	165 mm
Width	120 mm
Product weight	1.9 kg

Environment

IP degree of protection	IP40
Ambient air temperature for operation	-10...40 °C
Standards	IEC 2.2

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
