



Main

Range	Evx
Aesthetic name	Evx Ferro
Product or component type	Conversion kit
Function	Standard

Complementary

[Ue] rated operational voltage	230 V 50 Hz
Rated power in VA	5 VA
Battery capacity	4 Ah 6 V Ni-Cd (Nickel-Cadmium)
Charging time	1 h 2.1 h 2.45 s
Emergency luminous flux	100 % of nominal flux during 2 h 10 10 W G3 100 % of nominal flux during 1 h 20 W G3 10 % of nominal flux during 2 h 45 20 W G3 10 % of nominal flux during 1 h 50 W GY6.35
Bulb type	Halogen lamp
Electrical insulation class	Class II
Connections - terminals	Screw terminal
Height	Battery : 33 mm Circuit : 32 mm
Width	Battery : 332 mm Circuit : 183 mm
Depth	Circuit : 40.5 mm Battery : 34 mm
Product weight	0.25 kg 0.75 kg

Environment

Fire resistance	750 °C
Standards	CEI 50-11

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------