

# Product data sheet

Specifications



Emergency luminaire, Exiway Smartduo, Dicube, 1h, 2x1200lm, non maintained, black

OVA48060

## Main

Range Of Product	Exiway
Range	Exiway Smartduo
Product Name	Exiway Smartduo DiCube
Product Or Component Type	Emergency light fitting
Device Application	Anti-panic lighting
Function	Addressable
Supply	Non-maintained
Colour	Black
Light Source	LED 3 W x 6 (100000 h) each headlight
Light Source Colour	White
Cover Type	Transparent
Number Of Batteries	1 x 12.8 V 6.4 Ah LiFePO4
Wiring Device Additional Information	Searchlights rotate on their axis from 90° to 45°

## Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Power Consumption In Va	11 VA
Electrical Insulation Class	Class II
Autonomy	1 h
Charging Time	12 h
Luminous Flux	Emergency condition: 2400 lm
Visibility Distance	20 m
Material	Polycarbonate Thermoplastic
Device Mounting	Surface ceiling Surface wall
Height	253 mm
Width	406 mm
Depth	170 mm
Net Weight	3.4 kg
Market Segment	Industrial buildings

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	EN 60598-2-22 EN 62034

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	28.0 cm
Package 1 Length	40.5 cm
Package 1 Weight	3.204 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	32.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	37.632 kg

## Contractual warranty

Warranty	18 Months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>