



Overview

Model Name	APC Essential SurgeArrest 1 outlet with Phone Protection 230V Spain
Includes	1.8 Meter Tel cable (2) , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Portugal , Spain

Output

Number of Outlets	1
Receptacle Style	CEE 7 Schuko

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz
Input Connections	Schuko CEE 7/7P
Maximum Line Current per phase	16.0 A

Surge Protection and Filtering

Surge energy rating	960 Joules
EP Joule Rating	1060 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	20.0 dB
Peak Current Normal Mode	13 kA
Peak Current Common Mode	13.0 kA
Data Line Protection	Analog phone line for phone/fax/modem/DSL (RJ-11 connector)
Let Through Voltage Rating	900

Physical

Net Weight	0.1 kg
Maximum Height	94.0 mm
Maximum Width	70.0 mm
Maximum Depth	76.0 mm

Shipping Weight	0.1 kg
Shipping Height	114.0 mm
Shipping Width	89.0 mm
Shipping Depth	83.0 mm
Master Carton Units	12.0
Master Carton Weight	3.0 lbs
SCC Codes	1073130422776 9
Color	Charcoal
Units per Pallet	648.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CE
Standard warranty	3 years (all other countries) , Lifetime
Equipment protection policy	Lifetime : 50000 Euros
UL 1449 TVSS Rating	--

Sustainable Offer Status

RoHS	Compliant
------	-----------