



Overview

Model Name	APC Essential SurgeArrest 1 Outlet Wall Mount with Dual USB Ports (5V/2.4A), 230V Australia
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Australia , New Zealand

Output

Number of Outlets	1
Receptacle Style	Australia/New Zealand

Input

Nominal Input Voltage	240V
Input Power	2400 W
Input Frequency	50 Hz
Input Connections	Australian/Chinese
Maximum Line Current per phase	10.0 A
Maximum Input Current	10 A

Surge Protection and Filtering

Surge energy rating	306 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	12 kA
NM Surge Response Time (ns)	1.0 NS
Data Line Protection	--
Data Lines Protected(multi-line only)	--

Physical

Net Weight	0.12 kg
Maximum Height	113.0 mm
Maximum Width	58.0 mm

Maximum Depth	60.0 mm
Shipping Weight	0.19 kg
Shipping Height	177.0 mm
Shipping Width	112.0 mm
Shipping Depth	65.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	14.76 x 12.01 x 5.51 inches
Master Carton Weight	2.3 kg
SCC Codes	1073130433716 1
Color	White
Units per Pallet	648.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	RCM , SAA
Standard warranty	Lifetime
Equipment protection policy	Lifetime : 75000 AUD
UL 1449 TVSS Rating	500

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs