



Overview

Model Name	APC Essential SurgeArrest 5 Outlets, 3 Meter cord, 230V Korea
Includes	User Manual , Warranty card
Standard Lead Time	Usually in Stock
Product Distribution	KOREA, REPUBLIC OF

Output

Number of Outlets	5
Receptacle Style	CEE 7 Schuko

Input

Input Frequency	47 - 63 Hz
Input Connections	Schuko CEE 7/7P
Cord Length	3 meters
Maximum Input Current	10 A

Surge Protection and Filtering

Surge energy rating	903 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	30.0 dB
Peak Current Normal Mode	26 kA
Peak Current Common Mode	26.0 kA
Data Line Protection	--
Let Through Voltage Rating	900

Physical

Net Weight	0.69 kg
Maximum Height	45.0 mm
Maximum Width	389.0 mm
Maximum Depth	70.0 mm
Shipping Weight	0.75 kg

Shipping Height	47.0 mm
Shipping Width	425.0 mm
Shipping Depth	130.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	14 x 11 x 18 inches
Master Carton Weight	12.0 kg
SCC Codes	1073130429166 1
Color	Black

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %

Conformance

Approvals	KCC
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs