



Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 3x1 Pole 3 Wire 20A 240V IEC309 680cm 860cm 1040cm
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada , Japan , United States

Output

Nominal Output Voltage	240V
Maximum Total Current Draw per Phase	20 A
Output Connections	(3) IEC 309 20A (Battery Backup)

Input

Nominal Input Voltage	240V
Input Frequency	60 Hz
Maximum Line Current per phase	20 A

Physical

Net Weight	6.82 kg
Maximum Height	152.0 mm
Maximum Width	432.0 mm
Maximum Depth	419.0 mm
Shipping Weight	7.73 kg
Shipping Height	152.0 mm
Shipping Width	432.0 mm
Shipping Depth	419.0 mm
Color	Light grey

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Approvals	UL Listed
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------
