



Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 3x1 Pole 3 Wire 20A 250V L5-20 UL 260cm 380cm 500cm
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada , Japan , United States

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	20 A
Output Connections	(3) NEMA L5-20R (Battery Backup)

Input

Nominal Input Voltage	208 3PH
Input Frequency	60 Hz
Maximum Line Current per phase	20 A

Physical

Net Weight	1.59 kg
Maximum Height	127.0 mm
Maximum Width	445.0 mm
Maximum Depth	406.0 mm
Shipping Weight	2.5 kg
Shipping Height	127.0 mm
Shipping Width	445.0 mm
Shipping Depth	406.0 mm
Color	Black

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Approvals	UL Listed
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------
