



Overview

Model Name	APC Audio-Video SurgeArrest 8 outlet with Phone and Coax, 230V UK
Includes	1.8 Meter Tel cable (2) , 60 cm coaxial cable , User Manual
Standard Lead Time	Usually in Stock

Output

Number of Outlets	8
Receptacle Style	UK BS1363 plug

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz
Input Connections	British BS1363A
Maximum Line Current per phase	13.0 A
Cord Length	3.05 meters

Surge Protection and Filtering

Surge energy rating	2525 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	70.0 dB
Peak Current Normal Mode	40 (/PH) kA
Peak Current Common Mode	30.0 kA
Data Line Protection	Co-axial Video / Cable protection , RJ-11 2-Way Modem/Fax/DSL splitter with protection (four wire dual lines)
Data Lines Protected(multi-line only)	1-4
Let Through Voltage Rating	700

Physical

Net Weight	1.23 kg
Maximum Height	372.0 mm
Maximum Width	122.0 mm
Maximum Depth	42.0 mm

Shipping Weight	1.32 kg
Shipping Height	381.0 mm
Shipping Width	216.0 mm
Shipping Depth	51.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	27.0 inches
Master Carton Weight	15.91 kg
SCC Codes	1073130424354 7
Color	Silver
Units per Pallet	60.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CE , WEEE
Standard warranty	5 years (all other countries) , Lifetime (European Union countries only)
Equipment protection policy	Lifetime : 25000 GBP

Sustainable Offer Status

RoHS	Compliant
------	-----------