



⚠ Discontinued

## Commercial status

Discontinued: 13 June 2017

has not been replaced. Please contact your customer care center for more information.

## Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Product specific application	Site project
Enclosure type	Enclosure for power outlet

## Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	8
Total number of 18 mm modules	8
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Number of openings of interface	4
Protection device type	1 iLD residual current circuit breaker (RCCB) - 40 A - 2P - 30 mA 2 DT40N miniature circuit breaker (MCB) - 16 A - 1P + N - 10 kA
Local signalling	Indicator light voltage indication
Control button type	Emergency stop
Other equipments	plug - 1 2P + E 16 A 230 V power cord - 1 handle - 1 socket-outlet - 4 2P + E 16 A 230 V
Type of front cover	Transparent
[In] rated current	16 A
Type of rail	DIN
Number of terminal blocks	1 with 8 outgoing
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Net weight	3.5 kg
Width	280 mm
Height	510 mm
Depth	160 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 61439-4
Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Overvoltage category	II
Ambient air temperature for operation	-25...40 °C