

# Product data sheet

Specifications



## PratiKa plug - screw - angled - 16A - 3P + E - 380...415 V AC - wall

PKE16W434

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	PratiKa
Product Or Component Type	Plug
Device Short Name	PratiKa plug
Plug, Socket Category	Low voltage
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Mounting Mode	Wall-mounted
Plug, Socket, Control Station Shape	Angled
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: nickel plated brass Screws: stainless steel
Connections - Terminals	Captive screws, completely loosened
Cable Cross Section	1...4 mm <sup>2</sup>
Cable Outer Diameter	21.5 mm
Thread Type	M25
Net Weight	0.19 kg
Base Dimension	123 x 75 mm
Height	123 mm
Width	75 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60309-2 IEC 60309-1
Ip Degree Of Protection	IP44 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C ( 86400 s )

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	7.5 cm
Package 1 Length	13 cm
Package 1 Weight	169 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	17 cm
Package 2 Width	26 cm
Package 2 Length	27 cm
Package 2 Weight	1.514 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	16
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.515 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations