

# Product data sheet

Specifications



## Wander socket outlet, Mureva PK, 16A, 3P+E, 400V, IP67

PKF16M734

### Main

Range	Mureva
Product Or Component Type	Wander socket
Device Short Name	Mureva screw
Plug, Socket Category	Low voltage
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Captive screws
Cable Cross Section	1...4 mm²
Cable Outer Diameter	8...15 mm
Cable Entry	Cable gland
Thread Type	Pg 21
Net Weight	0.2 kg
Height	87 mm
Width	87 mm
Depth	152 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

### Environment

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK08 conforming to EN 62262
<b>Fire Resistance</b>	850 °C conforming to IEC 60695-2-1
<b>Relative Humidity</b>	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
<b>Ambient Air Temperature For Operation</b>	35 °C ( 86400 s ) -25...40 °C

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	8.5 cm
<b>Package 1 Width</b>	9.0 cm
<b>Package 1 Length</b>	16.0 cm
<b>Package 1 Weight</b>	196.0 g
<b>Unit Type Of Package 2</b>	BB1
<b>Number Of Units In Package 2</b>	10
<b>Package 2 Height</b>	18.2 cm
<b>Package 2 Width</b>	26.4 cm
<b>Package 2 Length</b>	26.8 cm
<b>Package 2 Weight</b>	2.148 kg
<b>Unit Type Of Package 3</b>	S03
<b>Number Of Units In Package 3</b>	20
<b>Package 3 Height</b>	30.0 cm
<b>Package 3 Width</b>	30.0 cm
<b>Package 3 Length</b>	40.0 cm
<b>Package 3 Weight</b>	4.783 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations