

Product data sheet

Specifications



PratiKa socket - screw - straight - 32 A - 3P+E - 400..440 V AC - panel - IP67

PKF32G7C4

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	PratiKa
Product Or Component Type	Socket for container
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Industrial Socket Type	Screw
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Panel-mounted
Plug, Socket, Control Station Shape	Straight
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	400...440 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	3 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Screw terminal block
Cable Cross Section	2.5...10 mm²
Cable Outer Diameter	11.5...21 mm
Net Weight	0.26 kg
Base Dimension	90 x 100 mm
Height	100 mm
Width	95 mm
Depth	127 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60309-1 EN 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	-25...40 °C 35 °C (86400 s)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	9.5 cm
Package 1 Length	10 cm
Package 1 Weight	275 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15.5 cm
Package 2 Width	21 cm
Package 2 Length	27 cm
Package 2 Weight	1.65 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	12
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.367 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations