

Product data sheet

Specifications



PratiKa socket - screw - angled - 32A - 2P + E - 380...415 V AC - wall

PKF32W733

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	PratiKa
Product Or Component Type	Socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Poles Description	2P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Wall-mounted
Plug, Socket, Control Station Shape	Angled
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	9 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Captive screws
Cable Cross Section	2.5...10 mm²
Cable Outer Diameter	21 mm
Thread Type	M25
Height	191 mm
Width	90 mm
Depth	119 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	750 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.4 cm
Package 1 Width	9.5 cm
Package 1 Length	16.1 cm
Package 1 Weight	366 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	17 cm
Package 2 Width	27 cm
Package 2 Length	26.3 cm
Package 2 Weight	1.83 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	10
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.987 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations