

# Product data sheet

## Characteristics

# PKX32M734

PratiKa wander plug - straight - 32 A - 3P + E -  
380...415 V AC - IP67



### Main

Range	PratiKa
Product or component type	Wander plug
Device short name	PratiKa plug
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

### Complementary

Plug, socket, control station shape	Straight
[In] rated current	32 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Brass sleeves :
Connections - terminals	Fast connection
Cable cross section	2.5...6 mm <sup>2</sup>
Cable outer diameter	11.5...21 mm
Cable entry	Fair lead Cable gland
Thread type	Pg 21
Height	152 mm
Width	95 mm
Depth	95 mm
Colour	Grey ( RAL 7035 )
Voltage colour	Red

### Environment

Standards	IEC 60309-2 IEC 60309-1
-----------	----------------------------

IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Relative humidity	50 % ( 40 °C ) 70 % ( 30 °C ) 90 % ( 20 °C )
Operating altitude	2000 m
Ambient air temperature for operation	35 °C ( 86400 s ) -25...40 °C

### Contractual warranty

Warranty period	18 months
-----------------	-----------