

PMM500-ALA

Power Management Module- 500kVA, Aluminum transformer 480V-IN 400V/208V-OUT, Configurable



Overview

Model Name	Power Management Module- 500kVA, Aluminum transformer 480V-IN 400V/208V-OUT, Configurable
Includes	Installation guide , Integrated network management
Product Distribution	United States

Output

Nominal Output Voltage	208V , 400 3PH
------------------------	----------------

Input

Nominal Input Voltage	480 3PH
Input Frequency	60 Hz
Maximum Input Current per phase	601 A

Physical

Net Weight	2218.06 kg
Maximum Height	2032.0 mm
Maximum Width	1524.0 mm
Maximum Depth	1092.0 mm
Shipping Weight	2549.19 kg
Shipping Height	2426.0 mm
Shipping Width	1859.0 mm
Shipping Depth	1450.0 mm
Color	White

Environmental

Operating Environment	-10 - 40 °C
Operating Relative Humidity	10 - 70 %
Operating Elevation	0-1980 meters
Storage Temperature	-25 to 55 °C

Storage Relative Humidity	10 - 90% non-condensing %
Storage Elevation	@ERROR-150 meters

Conformance

Approvals	CSA C22.2 No. 60950 , DOE2016 / NRCan , FCC Part 15 Class A , OSHPD , UL 60950-1 , UL 891 , cULus
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
