



### Overview

Model Name	Power Management Module- 500kVA, Copper transformer 480V-IN 208V-OUT, Configurable
Includes	Installation guide , Integrated network management
Product Distribution	United States

### Output

Nominal Output Voltage	208 3PH
------------------------	---------

### Input

Nominal Input Voltage	480 3PH
Input Frequency	60 Hz
Maximum Input Current per phase	601 A

### Physical

Net Weight	2267.96 kg
Maximum Height	2032.0 mm
Maximum Width	1524.0 mm
Maximum Depth	1092.0 mm
Shipping Weight	2599.08 kg
Shipping Height	2426.0 mm
Shipping Width	1859.0 mm
Shipping Depth	1450.0 mm
Color	White

### Environmental

Operating Environment	-10 - 40 °C
Operating Relative Humidity	10 - 70 %
Operating Elevation	0-1980 meters
Storage Temperature	-25 to 55 °C
Storage Relative Humidity	10 - 90% non-condensing %
Storage Elevation	@ERROR-150 meters

**Conformance**

Approvals	CSA C22.2 No. 60950 , DOE2016 / NRCan , FCC Part 15 Class A , OSHPD , UL 60950-1 , UL 891 , cULus
Standard warranty	1 year repair or replace

**Sustainable Offer Status**

RoHS	Compliant
REACH	REACH: Contains No SVHCs