

# Product data sheet

Specifications



## Pragma surface enclosure - IP30 - 4 x 13 modules - without door

PRA10204

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	336 mm outside:
Height	750 mm outside:
Depth	123 mm outside:
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	4
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type Of Door	Without

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	26
Total Number Of 18 Mm Modules	52
Power Dissipation In W	53 W
[In] Rated Current	90 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Trunking Cut-out plates Cable or tube Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 29 outgoing
Distribution Block Outgoers	4 x 25 mm <sup>2</sup> for earth 25 x 4 mm <sup>2</sup> for earth
Enclosure Material	Back part: technoplastic Front face: technoplastic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted Country	Denmark Spain
Embedding Depth	0 mm
Internal Depth	95 mm

## Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	42.0 cm
Package 1 Length	83.0 cm
Package 1 Weight	4.65 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	95.7 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations