



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	550 mm
Height	450 mm
Depth	148 mm
Nb of 18 mm modules per row	24
Nb of horizontal rows	2
Electrical insulation class	Class II Double insulation
Provided equipment	Marking kit (1) Identification label (1) Terminal block (1) Blanking plate strip (1)

Complementary

Enclosure mounting	Surface
9 mm pitches	48
Total number of 18 mm modules	48
Power dissipation in W	67 W
[In] rated current	125 A
Type of rail	DIN
Cable entry	Cable or tube Cut-out plates Removable plates Trunking
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth terminal block with 35 Quick outgoers
Distribution block outgoers	1 x 50 mm ² for earth

	2 x 25 mm ² for earth 32 x 6 mm ² for earth
Enclosure material	Back part : technoplastic Front face : technoplastic Back part : metal Front face : metal
Colour	Enclosure : white (RAL 9016) Front face : grey (RAL 7004)
Targeted country	Denmark Norway France Belgium

Environment

Fire resistance	Back part : 750 °C conforming to IEC 60695-2-1 Front face : 750 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-24 IEC 60670-1 IEC 61439-1 IEC 61439-3 IEC 60998

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------