

Product data sheet

Specifications



Pragma surface enclosure - IP40 - 3 x 18 modules - transparent door

PRA13783

⚠ Discontinued on: Mar 23, 2020

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	426 mm outside:
Height	600 mm
Depth	145 mm
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	3
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Total Number Of 18 Mm Modules	54
Power Dissipation In W	56 W
[In] Rated Current	125 A
Type Of Rail	DIN
Cable Entry	Trunking Cut-out plates Removable plates Cable or tube
Number Of Terminal Blocks	1 earth (Quick) with 26 outgoing
Distribution Block Outgoers	2 x 25 mm ² for earth 24 x 6 mm ² for earth
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Fire Resistance	Back part: 750 °C conforming to IEC 60695-2-1 Door: 750 °C conforming to IEC 60695-2-1 Front face: 750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	EN 60439-3 IEC 62262 EN 60695-2-11 IEC 60947-7-1 IEC 60529 IEC 60695-2-11 IEC 60439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	51 cm
Package 1 Length	68 cm
Package 1 Weight	6.2 kg

Contractual warranty

Warranty	18 months
----------	-----------