

# Product data sheet

Specifications



## Pragma recessed enclosure - 3 x 24 modules - 160 A - without door

PRA22324

⚠ Discontinued on: Apr 4, 2024

⚠ Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	630 mm wall: 660 mm outside:
Depth	30 mm outside: 95 mm wall:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	3
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type Of Door	Without

### Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	72
Power Dissipation In W	90 W
[In] Rated Current	160 A
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Cable or tube Side pre-cutouts Removable plates
Comb Busbar And Distribution Block Compatibility	XE compatible
Number Of Terminal Blocks	1 earth (Quick) with 35 outgoing
Distribution Block Outgoers	2 x 25 mm² for earth 32 x 6 mm² for earth 1 x 50 mm² for earth

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted Country	Belgium France
Embedding Depth	95 mm
Internal Depth	93 mm

## Environment

Fire Resistance	Front face: 750 °C Back part: 850 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	64.5 cm
Package 1 Length	68.5 cm
Package 1 Weight	11.7 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	105.6 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>