



## Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	930 mm wall: 960 mm outside:
Depth	30 mm outside: 95 mm wall:
Nb of 18 mm modules per row	24
Nb of horizontal rows	5
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip

## Complementary

Enclosure mounting	Flush
9 mm pitches	48
Total number of 18 mm modules	120
Power dissipation in W	133 W
[In] rated current	160 A
Type of rail	DIN
Cable entry	Cable or tube Removable plates Side pre-cutouts
Comb busbar and distribution block compatibility	XE compatible

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of terminal blocks	1 earth (Quick) with 44 outgoing
Distribution block outgoing	40 x 6 mm <sup>2</sup> for earth 1 x 50 mm <sup>2</sup> for earth 3 x 25 mm <sup>2</sup> for earth
Enclosure material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	France Belgium

## Environment

Fire resistance	Front face: 750 °C Back part: 850 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------