



### Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	486 mm
Height	780 mm wall: 810 mm outside:
Depth	86 mm wall: 43 mm outside:
Nb of 18 mm modules per row	18
Nb of horizontal rows	4
Electrical insulation class	Class II Double insulation
Provided equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type of door	Transparent Customizable

### Complementary

Enclosure mounting	Flush
9 mm pitches	36
Total number of 18 mm modules	72
Power dissipation in W	100 W
[In] rated current	125 A
Type of rail	DIN
Cable entry	Cable or tube Removable plates Side pre-cutouts
Number of terminal blocks	1 earth (Quick) with 30 outgoers

	1 neutral (Quick) with 28 outgoers
Distribution block outgoers	1 x 25 mm <sup>2</sup> for earth 1 x 50 mm <sup>2</sup> for earth 28 x 6 mm <sup>2</sup> for earth 3 x 25 mm <sup>2</sup> for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: transparent
Market segment	Small commercial Residential

## Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1 Door: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------