

Product data sheet

Specifications



Pragma flush enclosure - IP40 - 2 x 24 modules - without door

PRA25224

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	480 mm wall: 510 mm outside:
Depth	30 mm outside: 95 mm wall:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	2
Electrical Insulation Class	Double insulation Class II
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Without

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	48
Power Dissipation In W	81 W
[In] Rated Current	125 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	Multifix
Mounting Plate Description	Without mounting plate
Cable Entry	Side pre-cutouts Cable or tube Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 27 outgoers 1 neutral (Quick) with 29 outgoers

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Distribution Block Outgoers	2 x 25 mm² for earth 24 x 6 mm² for earth 1 x 50 mm² for earth 1 x 50 mm² for neutral 24 x 6 mm² for neutral 4 x 25 mm² for neutral
Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Market Segment	Residential Small commercial
Targeted Country	Greece Czech republic Hungary Russia
Embedding Depth	95 mm
Internal Depth	93 mm

Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.500 cm
Package 1 Width	65.000 cm
Package 1 Length	54.000 cm
Package 1 Weight	9.800 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	188.400 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations