



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	486 mm
Height	630 mm wall: 660 mm outside:
Depth	86 mm wall: 23 mm outside:
Nb of 18 mm modules per row	18
Nb of horizontal rows	3
Electrical insulation class	Double insulation Class II
Provided equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip

Complementary

Enclosure mounting	Flush
9 mm pitches	36
Total number of 18 mm modules	54
Power dissipation in W	68 W
[In] rated current	125 A
[Ui] rated insulation voltage	800 V
Type of rail	DIN
Cable entry	Side pre-cutouts Cable or tube Removable plates
Number of terminal blocks	1 earth (Quick) with 26 outgoing 1 neutral (Quick) with 24 outgoing

Distribution block outgoing	1 x 25 mm ² for earth 24 x 6 mm ² for earth 1 x 50 mm ² for earth 3 x 25 mm ² for neutral
Enclosure material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	Czech republic Hungary Greece Russia

Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------