

Product data sheet

Specifications



Pragma flush enclosure - IP40 - 1 x 18 modules - transparent door

PRA26118

 **Discontinued on:** Oct 27, 2020

 **Discontinued**

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	456 mm wall: 486 mm outside:
Height	330 mm wall: 360 mm outside:
Depth	86 mm wall: 43 mm outside:
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	36
Total Number Of 18 Mm Modules	18
Power Dissipation In W	45 W
[In] Rated Current	90 A
Type Of Rail	DIN
Cable Entry	Cable or tube Removable plates Side pre-cutouts
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Door: smoked Front face: white (RAL 9016)
Targeted Country	Italy

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	51 cm
Package 1 Length	38 cm
Package 1 Weight	3.42 kg

Contractual warranty

Warranty	18 months
----------	-----------