

Product data sheet

Specifications



Pragma flush enclosure - IP40 - 2 x 24 modules - transparent door

PRA26224

⚠ Discontinued on: Apr 4, 2024

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	480 mm wall: 510 mm outside:
Depth	95 mm wall: 55 mm outside:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	2
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	48
Power Dissipation In W	81 W
[In] Rated Current	125 A
Type Of Rail	Multifix
Mounting Plate Description	Without mounting plate
Cable Entry	Removable plates Cable or tube Side pre-cutouts
Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal Door: glass Door: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Targeted Country	Italy
Embedding Depth	95 mm
Internal Depth	93 mm

Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	65.0 cm
Package 1 Length	54.0 cm
Package 1 Weight	14.08 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations