

Product data sheet

Specifications



Pragma flush enclosure - IP40 - 4 x 18 modules - transparent door

PRA26418

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	456 mm wall: 486 mm outside:
Height	780 mm wall: 810 mm outside:
Depth	86 mm wall: 43 mm outside:
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	4
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	36
Total Number Of 18 Mm Modules	72
Power Dissipation In W	100 W
[In] Rated Current	125 A
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Cable or tube Side pre-cutouts Removable plates
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Door: smoked Front face: white (RAL 9016)
Targeted Country	Italy

Embedding Depth	86 mm
------------------------	-------

Internal Depth	84 mm
-----------------------	-------

Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
------------------------	---

Ip Degree Of Protection	IP30 without door IP40 with door
--------------------------------	-------------------------------------

Ik Degree Of Protection	IK08 without door IK09 with door
--------------------------------	-------------------------------------

Overvoltage Category	II
-----------------------------	----

Ambient Air Temperature For Operation	-25...60 °C
--	-------------

Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3
------------------	---

Packing Units

Unit Type Of Package 1	PCE
-------------------------------	-----

Number Of Units In Package 1	1
-------------------------------------	---

Package 1 Height	18.5 cm
-------------------------	---------

Package 1 Width	51.0 cm
------------------------	---------

Package 1 Length	83.0 cm
-------------------------	---------

Package 1 Weight	8.13 kg
-------------------------	---------

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Circularity Profile No need of specific recycling operations
