

Product data sheet

Specifications



Pragma surface enclosure - IP30 - 2 x 24 modules - plain door

PRA30224

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	550 mm outside:
Height	450 mm
Depth	173 mm
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	2
Electrical Insulation Class	Class II Double insulation
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Plain

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	48
Total Number Of 18 Mm Modules	48
Power Dissipation In W	67 W
[In] Rated Current	125 A
Type Of Rail	Multifix
Cable Entry	Trunking Cut-out plates Cable or tube Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 27 outgoing 1 neutral (Quick) with 29 outgoing
Distribution Block Outgoers	2 x 25 mm ² for earth 24 x 6 mm ² for earth 1 x 50 mm ² for earth 1 x 50 mm ² for neutral 24 x 6 mm ² for neutral 4 x 25 mm ² for neutral

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Door: white (RAL 9016) Enclosure: white (RAL 9016) Front face: grey (RAL 7004)

Environment

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	65.0 cm
Package 1 Length	54.0 cm
Package 1 Weight	14.22 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations