

Product data sheet

Specifications



Pragma flush enclosure - IP30 - 1 x 13 modules - without door

PRA32113

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	366 mm wall: 396 mm outside:
Height	330 mm wall: 360 mm outside:
Depth	86 mm wall: 21 mm outside:
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip 3 x terminal block
Type Of Door	Without

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	26
Total Number Of 18 Mm Modules	13
Power Dissipation In W	34 W
[In] Rated Current	63 A
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Removable plates Cable or tube Side pre-cutouts
Comb Busbar And Distribution Block Compatibility	XE compatible
Number Of Terminal Blocks	1 earth (Quick) with 14 outgoing 2 phase / neutral (Quick) with 7 outgoing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Distribution Block Outgoers	3 x 25 mm² for earth 11 x 4 mm² for earth 2 x 35 mm² for phase / neutral 12 x 16 mm² for phase / neutral
Enclosure Material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: white (RAL 9016)
Targeted Country	France
Embedding Depth	86 mm
Internal Depth	84 mm

Environment

Fire Resistance	Front face: 750 °C Back part: 850 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	42.000 cm
Package 1 Length	38.000 cm
Package 1 Weight	2.600 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	42
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	117.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile