

Product data sheet

Specifications



Pragma flush enclosure - IP30 - 4 x 24 modules - without door

PRA34424

❗ Discontinued on: May 6, 2019

❗ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	780 mm wall: 810 mm outside:
Depth	30 mm outside: 95 mm wall:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	4
Electrical Insulation Class	Double insulation Class II
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Without

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	96
Power Dissipation In W	110 W
[In] Rated Current	160 A
[Ui] Rated Insulation Voltage	800 V
Type Of Rail	Multifix
Cable Entry	Removable plates Side pre-cutouts Cable or tube
Number Of Terminal Blocks	1 earth (Quick) with 32 outgoing 1 neutral (Quick) with 35 outgoing
Distribution Block Outgoers	1 x 50 mm ² for earth 3 x 25 mm ² for earth 28 x 6 mm ² for earth 1 x 50 mm ² for neutral 28 x 6 mm ² for neutral 6 x 25 mm ² for neutral

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted Country	Finland Norway

Environment

Fire Resistance	Front face: 750 °C conforming to IEC 60695-2-1 Back part: 850 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	EN 60439-3 IEC 60695-2-11 IEC 60947-7-1 IEC 62262 IEC 60439-3 EN 60695-2-11 IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	65 cm
Package 1 Length	84 cm
Package 1 Weight	15.27 kg

Contractual warranty

Warranty	18 months
----------	-----------