

Product data sheet

Specifications



Pragma flush enclosure - IP30 - 6 x 24 modules - without door

PRA41624

❗ Discontinued on: May 6, 2019

❗ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	570 mm wall: 610 mm outside:
Height	1080 mm wall: 1110 mm outside:
Depth	30 mm outside: 95 mm wall:
Nb Of 18 Mm Modules Per Row	24
Nb Of Horizontal Rows	6
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type Of Door	Without

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	48
Total Number Of 18 Mm Modules	144
Power Dissipation In W	156 W
[In] Rated Current	160 A
[Ui] Rated Insulation Voltage	800 V
Type Of Rail	Multifix
Cable Entry	Cable or tube Removable plates Side pre-cutouts
Number Of Terminal Blocks	1 earth (Quick) with 32 outgoing
Distribution Block Outgoers	1 x 50 mm ² for earth 3 x 25 mm ² for earth 28 x 6 mm ² for earth

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted Country	Denmark

Environment

Fire Resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60529 EN 60439-3 IEC 60439-3 IEC 62262 EN 60695-2-11 IEC 60947-7-1 IEC 60695-2-11

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	65 cm
Package 1 Length	114 cm
Package 1 Weight	20.64 kg

Contractual warranty

Warranty	18 months
----------	-----------